

Skid Mounted Tubular Pasteurizer

Mfg:

Model:

Stock No. GMFP003.

Serial No. P-003-93

Skid Mounted Tubular Pasteurizer. S/N: P-003-93. Heat exchanger dimensions: 10 in. diameter x 61 in. L. (2) Condensate Tanks- 10 Gallon, MAWP: 125 psi at 210 °F. Unit is equipped with (2) electro-pneumatic valves and (2) Jordan pressure relief valves. Stainless Steel Balance Tank 30 Gallon. 2 in. inlet, (1) 3 in. Outlet, (2) 2 in. outlet. Inside dimensions 20 in. diameter, 24 in. depth. Overall dimensions: 43 in. L x 21 in. W x 37 in. H. Bell & Gossett Centrifugal Pump, Model: 11/28C, MAWP: 175 psi, capacity: 60 gpm at 50 ft, 1800 rpm maximum. Waukesha 30 positive displacement pump. (2) Dickson Temperature Chart Recorders. Model: KT602. S/N: 00252182, 01008504, Recorders feature touchpad controls and digital display. Single pen recorders with attached thermocouples. NIST: 5.1 °C, -7.3 °C, -8.3 °C. Input: 120 VAC, 16 watts, 60 Hz. Output: 9 VDC, 1 amp.







