

Waukesha 30 Positive Displacement Pump

Mfg: Waukesha

Model: 30

Stock No. 25.GO877201a

Serial No. 86556-SS

Waukesha 30 Positive Displacement Pump. Model: 30. S/N: 86556-SS. Capacity: 32.54 gpm. Displacement per revolution: 0.060 gal. Nominal capacity: 36 gpm. Maximum speed: 600 rpm. Baldor Industrial Motor, 2 hp, 1725 rpm, 208-230/460 V, 6.5-6.2/3.1 amps, 60 Hz, 3 phase. Nord Gear Drive, 3.18 ratio, 524 rpm (final). A-3 sanitary rated. 316 stainless steel body, cover and shafts. Components can be easily disassembled for COP cleaning. Typical applications: bakery, beverage, canning, confectionary, cosmetics, dairy, meat packing, pharmaceutical and aseptic. Inlets/outlets: (2) 1-1/2 in. dia. ACME fittings. Overall dimensions: 40 in. L x 13-1/2 in. W x 29 in. H.





