

## Chester Jensen Plate Heat Exchanger

Mfg: Chester Jensen

Model: 63 HMC

Stock No. GOB1251.7

Serial No. 11722304

Chester Jensen Plate Heat Exchanger. Model: 63 HMC, S/N: 11722304. Design pressure max: 100 psig. 316 Stainless steel plates: (170). Section 1: (108) plates; Section 2: (62) plates. Heat transfer surface area: 493 sq. ft. Fixed end ports: (4) 2-1/2 in. Movable end ports: (4) 2-1/2 in. Divider ports: (3) 2 in. Overall dimensions: 90 in. L x 25 in. W x 70 in. H. This unit came from Middlefield Cheese in Ohio. Running 7000 H/W of cheese milk 40°-113° F; 113°-165° F and 165°-192° F.

