

R-717 (AMMONIA) UNITS 4-FIN/INCH	MODELS						
	CO-201	CO-377	CO-504	CO-654	CO-787	CO-935	CO-1172
BASIC RATING BTU/HR RECIRC. OR FLOOD @ 1°FTD @ 12°FTD	2010 24120	3770 45240	5040 60480	6540 78480	7870 94440	9355 112200	11720 140640
DX @ 1°FTD @ 12°FTD	1710 20520	3205 38460	4285 51420	5560 66720	6775 81300	7950 95400	9965 119580
SQ. FT. FACE AREA	5.35	9.73	11.82	15.15	18.28	22.73	27.42
SQ. FT. TOTAL SURFACE	457	832	1011	1295	1563	1944	2345
AIR VOLUME CFM	2500	4870	6900	9100	11200	12550	16320
FANS & DIAMETER EACH	(1) 18	(2) 18	(3) 18	(4) 18	(5) 18	(3) 24	(4) 24
MOTORS & H.P. EACH	(1) 1/4	(2) 1/4	(3) 1/4	(4) 1/4	(5) 1/4	(3) 1/3	(4) 1/3
DIMENSION (INCHES)							
A. LENGTH OVERALL	61	92-1/2	107-1/2	131-1/2	154	131-1/2	154
B. WIDTH OVERALL	34-1/2	34-1/2	34-1/2	34-1/2	34-1/2	40	40
C. HEIGHT OVERALL	25	25	25	25	25	38-1/2	38-1/2
D. BOLT HOLE LOCATION	1/2	1/2	1/2	1/2	1/2	1/2	1/2
E. BOLT HOLE LOCATION	1-1/4	1-1/4	1-1/4	1-1/4	1-1/4	2-1/2	2-1/2
F. BOLT HOLE CENTERS	18-1/2	18-1/2	18-1/2	18-1/2	18-1/2	20	20
G. BOLT HOLE DIAMETER	13/16	13/16	13/16	13/16	13/16	13/16	13/16
H. DRAIN LOCATION	25-1/8	40-7/8	48-3/8	60-3/8	71-5/8	60-3/8	71-5/8
J. CONNECTION LOCATION	4	4	4	4	4	4	4
K. CONNECTION LOCATION	2	2	2	2	2	4	4
L. CONNECTION LOCATION	10-1/2	10-1/2	10-1/2	10-1/2	10-1/2	12-1/2	12-1/2
M. HANGER LENGTH	13-1/2	13-1/2	13-1/2	13-1/2	13-1/2	21	21
N. LIQUID CONN. MPT	3/4	3/4	3/4	3/4	3/4	3/4	3/4
P. SUCTION CONN. MPT	2	2	2	2	2	2	2
R. HOT GAS/OIL DRAIN MPT	3/4	3/4	3/4	3/4	3/4	3/4	3/4
S. DRAIN SIZE MPT	1-1/4	1-1/4	1-1/4	1-1/4	1-1/4	1-1/2	1-1/2
INTERNAL COIL VOLUME CU. FT.	.91	1.48	1.74	2.17	2.56	3.25	3.85
SHIPPING WGT. - APPROX. (LBS.)	750	1050	1250	1550	1750	1900	2210