

## Cleaver Brooks 250 hp Boiler

Mfg: Cleaver Brooks

Model: CB266-250

Stock No. HD-SC293.16a

Serial No. L-33038

Cleaver Brooks Packaged Boiler- 250 hp. Model CB266-250. S/N L-33038. Pressure-150 psi. Input- 1041000 BTU/hr natural gas; 74.5 gph oil. Gas-oil fired boiler, No. J516740. Marathon Electric Boiler Motor, Model AA-215TDR302DEW, frame 215, Type TDR-BYZ, 7-1/2 hp, 3 phase, 60 cycle, 1.15 SF, 208-220/440 V, 21/10.5 amp draw. At 60 hertz, motor runs at 1.15 SF/ 3,450 rpm; at 50 hertz, motor runs 1.0 SF/ 2840 rpm. General Control Hydramotor, Cat No. H10A620B5, Model A, SN RD3885, 120 V, 50/60 Freq., 125 VA. Cleaver Brooks control box, Type 26RJ8, Model CB-1, S/N 78527091, Code CBP/N 833-1157. Inlets/outlets- (2) 2-1/2 in., (8) 1 in., (5) 1-1/2 in., (1) 10 in., (2) 2 in., (3) 1/2 in., (1) 3 in. Manways-(2) 14 in. L x 11 in. W x 20 in. dia. Overall dimensions: 101 in. W x 198 in. L x 118 in. H.

