

Chester Jensen Falling Film Plate Chiller – 140Tons

Mfg: Chester Jensen

Model:

Stock No: HDAF525.56a

Serial No:

Chester Jensen Falling Film Plate Chiller. Cooling capacity: 140 tons at 224 gpm for a 26°F suction with a 15° TD. Total cooling section area: 299 sq. ft. (7) Plates with 32 corrugations each. S/N's: 66179, 36322, 36185, 36014, 47300, 36465, 47317. Nat'l Bd: 22943, 7150, 7050, 6963, 12943, 7243, 12947. Plate dimensions: 5 ft. L x 3 ft. 9 in. H. Reservoir tank: 280 gallons. Inside straight-wall dimensions: 5 ft. 10 in. L x 3 ft. 7 in. W x 1 ft. 10 in. H. Inlets: (1) 1-1/4 in. dia. FNPT, (1) 1-1/2 in. dia. liquid port, (1) 3 in. dia. liquid port, (1) 3 in. dia. refrigerant feed port. Outlets: (1) 1-1/4 in. dia. FNPT (drain), (1) 2 in. dia. FNPT (drain), (1) 2 in. dia. S-line (overflow), (1) 2 in. dia. S-line (discharge), (1) 2-1/2 in. dia. S-line (discharge), (1) 4 in. dia. S-line (discharge), (1) 4 in. dia. refrigerant suction port. Overall dimensions: 8 ft. 10 in. L x 4 ft. W x 8 ft. H.







