

## Alfa Laval Plate Heat Exchanger

Mfg: Alfa Laval

Model: H10-FMC

Stock No. HDAF531.79

Serial No. 4239

Alfa Laval Plate Heat Exchanger. Model: H10-FMC. S/N: 4239. Stainless steel plates: (255). Heat transfer surface area: approx. 1723 sq. ft. Maximum working pressure: 145 psig. Maximum working temperature: 285 °F. Fixed end ports: (2) 3 in. dia. ACME inlets. Dividers Inlets: (2) 3 in dia. ACME. Outlets: (3) 3 in. dia. ACME, (1) 2-1/2 in. dia. ACME. Terminal ports: (2) 4 in. dia. ACME. Overall dimensions: 11 ft. 3 in. L x 34 in. W x 97 in. H.



