

## Cherry Burrell Stellar Series Homogenizer

**Mfg: Cherry Burrell**

**Model: SS-3000-SGR-HD6**

**Stock No.: HDAF954.17**

**Serial No.: 83006**

Cherry-Burrell Stellar Series Homogenizer. Model: SS-3000-SGR-HD6 Stellar Series. S/N: 83006. Capacity: 1300 gph. Single-stage manual valve assembly. 1-1/2 in. dia. plungers. Spring loaded poppet seat valve cylinders. Maximum operating pressure: 3700 psi. Leeson Motor, 60 hp, 1740 rpm, 946 rpm (final), 208-230/460 V, 159-142/79 amps, 60 Hz, 3 phase. Inlets: (1) 2 in. dia. S-Line fitting. Outlets: (1) 1-1/2 in. dia. I-line fitting (reduces to 5/8 in.). Overall dimensions: 4 ft. 3 in. L x 3 ft. 2 in. W x 4 ft. 6 in. H. (ACN740).









