

Carlyle 6-Cylinder Reciprocating Compressor- 60 Ton

Mfg: Carlyle

Model: 5H60-A219

Stock No. HDBD134.7a

Serial No. 9262DVM

Carlyle 6-Cylinder Reciprocating Compressor- 60 Ton. Model: 5H60-A219. S/N: 9262DVM. Refrigerant: R-22, R-12. Nominal horsepower: 30-75 hp. Displacement @ 1750 rpm: 138.4 cfm. Stroke: 2-3/4 in. Bore: 3-1/4 in. Oil required: 21 pints. Fairbanks Motor, 50 hp, 1755 rpm, 220/440 V, 121/60.5 amps, 60 Hz, 3 phase. Oil separator, MAWP: 450 psi, 3/8 in. oil return. Oil heater. Non-water-cooled heads. Compressor suction: 3 in. diameter. Discharge: 2-1/2 in. diameter. Overall dimensions: 63 in. L x 40 in. W x 80 in. H.

