E.L. Nickell Ammonia Vertical Receiver- 140 Gallon	
Mfg: E.L. Nickell	Model: C-1930
Stock No.: HDCD305.3a	Serial No.: 2339

E.L. Nickell Ammonia Vertical Receiver- 140 Gallon. Model: C-1930. S/N: 2339. Nat'l Bd: 21428. Inside straight-wall dimensions: 2 ft. dia. x 6 ft. H. Maximum working pressure: 150 psi. Maximum working temperature: 650°F. Minimum working temperature: -20°F. Head radius: ELL 2:1. Head thickness: 1/4 in. Shell thickness: 3/16 in. Inlets/outlets: (2) 1 in. dia. ports, (1) 1-1/2 in. dia. port. (1) 2 in. dia. port. (1) 2 in. dia. port, (1) 3/4 in. dia. FNPT port, (1) 1/2 in. dia. port. Overall dimensions: 2 ft. 4 in. L x 2 ft. 4 in. W x 8 ft. 6 in. H.















