

## Waukesha Model 25 Positive Displacement Pump

Mfg: Waukesha

Model: 25 U1

Stock No: HDCF176.7

Serial No: DO47366SS

Waukesha 25 Positive Displacement Pump. Model: 25 U1. S/N: DO47366SS. Flow rate for new pump is 36 gpm with required horsepower and pressure. Discuss with salesperson your process and product to determine if this refurbished pump should handle your specific duty. Material of construction: 316 stainless steel. U.S. Electric Motor, 1 hp, 1730 rpm, 200-230/460 V, 5.2-5.0/2.5 amps, 60 Hz, 3 phase. U.S. Varidrive Module, Ratio: 2.25, 190/1900 rpm (min/max). Suitable to 200 psi (13.8 bar) differential pressure. Temperature range -40°F (-40°C) to 300°F (149°C). 1½" port size. 0-600 rpm speed range. Exclusive, non-galling Waukesha "88" alloy rotors. This pump is 3A and BISCC approved, features ease of disassembly for cleaning and flexible, three-way mounts. Inlets/outlets: (2) 1½ in. dia. ACME fittings. Overall dimensions: 3 ft. 6 in. L x 1 ft. 1 in. W x 2ft. 11 in. H.(ACN57).



