| APV Crepaco Multi-Flo Homogenizer | |
|-----------------------------------|-------------------|
| Mfg: APV Crepaco | Model: 5DL-770 |
| Stock No: HDDC319.60 | Serial No: E-6985 |

APV Crepaco Multi-Flo Homogenizer. Model: 5DL-770. S/N: E-6985. Output capacity: approximately 5000 gph at 2000 psi. Maximum rated pressure: 2000 PSI at 1200 and 900 rpm. Reliance Electric two-speed motor: 125 / 94 hp, 1190/890 rpm, 230 v, 302/248 a, 60 Hz, 3 phase. Hydraulic pump with two-speed Leeson motor: ½ hp, 1725/1425 rpm, 208-230/460 v, 2.0/2.2 a, 60/50 Hz, 3 phase. Features include: Tungsten carbide plungers, replaceable seats, a two-stage derby / hydro actuator, and high temperature warning sensor. (5) 2-1/2 in. dia. plunger. Inlets/outlets: (2) 3 in. ACME, (1) 2 in. MNPT. Overall dimensions: 6 ft. 9-1/2 in. L x 4 ft. 11 in. W x 7 ft. H.























































