

Chester Jensen Shell and Tube Pre-Heater

Mfg: Chester Jensen

Model: SV8 SS

Stock No

Serial No: 6204-C

Shell and Tube Heat Exchanger. Model: SV8 SS. S/N: 6204-C. Number of tubes: 18. Tube dimensions: 1-1/2 in. dia. x 80 in. L. Heat transfer surface area: approx. 47.12 sq. ft. Capacity: 11 gal. Aurora Pump, Model: L/H D4SBF- 114A, S/N: 98-07480. Dayton Motor, 1/2 hp, 1725 rpm, 230/460 V, 1.3/0.65 amps, 60 Hz, 3 phase. Inlets: (1) 1-1/2 in. dia. S-line (product), (1) 1-1/2 in. dia. FNPT (media). Outlets: (1) 1 in. dia. bevel with hex nut (media), (1) 1-1/2 in. dia. S-line (product). Overall dimensions: 86 in. L x 30 in. W x 74 in. H.







