

## Waukesha 25 Positive Displacement Pump

Mfg: Waukesha

Model: 25

Stock No. HDDF237.5a

Serial No. DO66742 SS

Waukesha 25 Positive Displacement Pump. S/N: DO66742 SS. Pump capacity: 25.38 gpm. Displacement per revolution: 0.060 gallons. Nominal capacity: 36 gpm. Pressure range: 200 psi. Maximum speed: 600 rpm. U.S. Motor, 3hp, 1730 rpm, 230/460 V, 11.0/5.5 amps, 60 Hz, 3 phase. U.S. Varidrive Module, 204/2036 min/max rpm, final speed (by test): 423 rpm. A-3 sanitary rated. Single o-ring seals. 316 stainless steel body, cover and shafts. Components can be easily disassembled for COP cleaning. Typical applications: bakery, beverage, canning, confectionary, cosmetics, dairy, meat packing, pharmaceutical and aseptic. Inlets/outlets: (2) 1-1/2 in. dia. threaded fittings. Overall dimensions: 40 in. L x 15 in. W x 26 in. H.



