

APV Crepaco Homogenizer

Mfg: APV Crepaco

Model: 5DD425

Stock No: HDDP129.14

Serial No: 2929

APV Crepaco Homogenizer. Model: 5DD425. S/N: 2929. Maximum capacity: 2,205 gph at 2,000 psi. Minimum capacity: 800 gph. 2-Stage manual valve assembly. Plunger Size: 1.437 in. Has tapered seat poppet valve cylinders. Reliance electric motor, 40 hp, 1775 rpm, 208 V, 107 amps, 60 Hz, 3 phase. Pulley ratio: 9.48. Final speed: 200 rpm. Inlets: (1) 2-1/2 in. dia. ACME fitting. Outlets: (1) 1-1/2 in. dia. ACME fitting. Overall dimensions: 5 ft. 6 in. L x 4 ft. W x 5 ft. 7 in. H.







