

BF Gump 48 in. Vibratory Sifter

Mfg: BF Gump

Model: CV-481

Stock No. HDDP144.3

Serial No. CV-2703

BF Gump Vibratory Sifter- 48 in. Model: CV-481, SN: CV-2703. (3) sifting stages. First stage: 45-1/2 in. dia. x 4 in. H sifting deck. Second stage: 45-1/2 in. dia. x 6 in. H sifting deck with 91-mesh wire sifting screen. Final stage: 45-1/2 in. dia. x 6 in. H sloping, sifting deck. Decks supported by (12) 1-3/4 in. dia. x 5 in. H springs. Baldor Industrial Motor, 1-1/2 hp, 1140 rpm, 230/460 V, 4.6/2.3 amps, 60 Hz, 3 phase. Inlets: (1) 7 in. dia. infeed, (1) 9 in. dia. infeed. Outlet: (3) 8 in. dia. discharge chutes. Overall dimensions: 54 in. L x 48 in. W x 70 in. H.



