

Vacu Fresh Vacuum Sealer

Mfg: Vacu Fresh

Model: I-20 Webomatic

Stock No. HDFD447.10

Serial No. _____

Vacu-Fresh Vacuum Sealer. Model: I-20 Webomatic. Top overhead sight glass. Twin removable seal bars located on either side of top lid infeed. Inside suction bay dimensions: 2 ft. 10 in. L x 2 ft. 4 in. W x 5 in. H. Busch Vacuum Pump. Type: 100-132. S/N: 152104. Vacuum: .05 mbar. (2) Katt Electric Motors, 4 hp, 1710 rpm, 230/460 V, 11.2/5.6 amps, 60 Hz, 3 phase. Inlet: 34 in. L x 28 in. W. (top lid infeed). Outlet: (1) 1 ½ in. dia. port (suction). Overall dimensions: 3 ft. 4 in. L x 3 ft. W x 3 ft. 4 in. H.





Type 100-132-152104
 Vacuum 0,5 mbar
 Motor Oil Type SAE 30
 Qt. 2 Ltr.
 in West Germany

VDE.0530 IP 24 Is. Kl. I
 Nr. 589-430 USA
 Typ 100L cos φ 0,8 ~ 50
 KW 3 KW 2,5
 V 230Y/460Y V 208Y/415Y
 A 11,2 / 5,6 A
 n 1710 n

Made in West Germany

ELEKTROMASCHINENBAU Wittlich
 Elektromaschinenbau Wittlich GmbH, Werkstr. 8, 5560 Wittlich 18, Tel.: 065 71/2004-7, Telex: 4721726
 Iso.kl T4UE ED 004
 Typ KTI 1,5 Nr. 11361785
 KVA 1,2 Hz 50/60
 prU 208-440 A
 seU 38/48 V/220 A
 nVDE 10550 IP 00