

Fristam High Pressure Sanitary Pump


Mfg: Fristam

Model: FM332-175

Stock No. HDLF001.

Serial No. FM332 74005

Fristam High Pressure Sanitary Pump. Model FM332-175, S/N FM332 74005. Inlet/ outlet 2.5 in. Pump is three stages and is designed to pump up to 200 gpm at 200 psi and 500 feet of head, with 60 hp Baldor motor, 3,550rpm, 230/460 V, 60hz, 3-phase.







FM & CCFM 3500 RPM Composite Performance Curve

Performance curves based on tests using 70°F water. A tolerance of $\pm 5\%$ applies to all figures.

