

## Tri Clover SolidC Centrifugal Pump

Mfg: Tri Clover

Model: CL3295MDG-213/215TC

Stock No. HDMD126.3a

Serial No. 462448-01

Tri Clover SolidC Centrifugal Pump. Model: CL3295MDG-213/215TC. S/N: 462448-01. Pump capacity: 250 gpm. Maximum inlet pressure: 145 psi. Temperature range: 14°F to 284°F. External balanced seal. Sterling Electric Motor, 7.5 hp, 1760 rpm, 230/460 V, 18.9/9.5 amps, 60 Hz. The SolidC pump is designed for standard duty applications, like pumping CIP solutions, utilities, water (processing, heating, cooling), washing machines and simple transport duty within working range. Suited for use in the food, dairy, beverage, personal care, light chemical and water industries. Inlet: 3 in. 'S' line. Outlet: 2 in. 'S' line. Overall dimensions: 25 in. L x 16 in. W x 19 in. H.



