

Dunham-Bush Boiler Feed Pump System

Mfg: Dunham-Bush

Model: PCHPD1468

Stock No: HDNW103.4

Serial No: 77850

Dunham-Bush Boiler Feed Pump System. Model: PCHPD1468. S/N: 77850. 1994 Cemline Corp. Shell and Tube Heat Exchanger, S/N: 45450, MAWP: 150 psi @ 500°F, MDMT: -20°F @ 150 psi, tube material: carbon steel, number of passes: 3, number of tubes: 237, tube dimensions: 11/16 in. dia. x 9 ft. 6 in. L, heat transfer surface area: approx. 405 sq. ft., tube volume: 43.35 gal. Stoystown Tank and Steel Co. Liquid Storage Tank- 75 Gallon, S/N and Nat'l Bd: 57750, MAWP: 125 psi @ 650°F, MDMT: -20°F @ 125 psi. Centrifugal Pump with Lincoln Electric Motor, 5 hp, 1740 rpm, 230/460 V, 13.6/6.8 amps, 60 Hz, 3 phase. Centrifugal Pump with Baldor Industrial Motor, 5 hp, 1725 rpm, 208-230/460 V, 14.8-14/7 amps, 60 Hz, 3 phase. Condensate Steam Trap, Nat'l Bd: 7667, MAWP: 125 psi @ 375°F, MDMT: -20°F @ 125 psi. Inlets: (1) 4 in. dia. 150lb. ANSI flanged port (product), (1) 8 in. dia. 150lb. ANSI flanged port (media). Outlets: (1) 2 in. dia. 150lb. ANSI flanged port (condensate), (1) 4 in. dia. 15lb. ANSI flanged port (product). Overall dimensions: 11 ft. 10 in. L x 7 ft. W x 7 ft. H.





