

## Viking Heavy-Duty Series Rotary Pump

Mfg: Viking

Model: KK4225

Stock No. HDPH437.2a

Serial No. 10366316

Viking Heavy-Duty Series Rotary Pump. Model: KK4225. S/N: 10366316. Cast iron and steel construction. Previously used by M&M/Mars to pump chocolate. Test speed: 285 rpm. Capacity at test speed: 36.5 gpm. Nominal speed: 640 rpm. Nominal capacity: 80 gpm. Reliance Electric Motor, 2 hp, 1160 rpm, 230/460 V, 9.5-8.6/4.3 amps, 3 phase. Viking Helical Gear Reducer with lo/hi speeds, (6) gear ratios: 2.76 to 1 to 7.65 to 1. The Viking positive displacement jacketed rotary pump provides an even flow when handling heavy, viscous liquids like asphalt, syrup, molasses, coal tar, soap solutions, etc. Inlets: (1) 2 in. dia. NPT (female). Outlets: (1) 2 in. dia. NPT (female). Overall dimensions: 59 in. L x 19 in. W x 15 in. H.



