

Graco President 10:1 Ratio Drum Pump

Mfg: Graco

Model: 206-445 Series "G"

Stock No: HDPH639.2a

Serial No:

(4) Graco President 10:1 Ratio Drum Pump s. Model: 206-445 Series "G". Capacity: 3 gpm max.(60 cycles/min.) Stainless steel wetted parts. Max Air PSI: 180. Fluid to air pressure ratio 10:1. Piston dimensions: 1 in. dia. x 25-1/2 in. L. Luftmotor-air motor, Model: 207-352, S/N's: J3E, C3E, H3E, J3E. Air Inlet: (1) 1 in. dia FNPT, (1) 1-1/2 in. dia. FNPT (product). Outlet: (1) 1-1/2 in. dia. FNPT (product). Overall dimensions: 3 ft. 7 in. L x 9 in. W x 8 in. H. (ACN29).





