

## Viking Rotary Gear Pump

Mfg: Viking

Model: KK288

Stock No. HDPH648.2a

Serial No. 0608088

Viking Rotary Gear Pump. Model: KK288. S/N: 0608088. Capacity: 60 gpm. Displacement per revolution: 0.14070 gal. US Electrical Motor, 5 hp, 1800 rpm, final rpm 430, 208-230/460 V, 14.8-14.0/7.0 amps, 60 Hz, 3 phase. Inlets/outlets: (2) 2 in. dia. FNPT. Overall dimensions 54-1/2 in. L x 16-1/2 in. W x 15 in. H.

