

Waukesha U1-series Positive Displacement Pump

Mfg: Waukesha

Model: 30 U1

Stock No. HDSC063.11a

Serial No. 142864

Waukesha U1-series Positive Displacement Pump. Model: 30 U1. S/N: 142864. Nominal Capacity: 36 gpm. Displacement per Revolution: 0.060. Seal Option: Single O-Ring. Stainless Steel Sleeve. Buna Elastomers. Nord Gear Corporation Motor and Drive, 2 hp, 1725/261 rpm, 208-230/460 V, 6.6-6.2/3.1 amps, 60 Hz, 3 phase. Inlets/outlets: (2) 1 ½ in. dia. S-line fittings. Suitable to 200 psi (13.8 bar) differential pressure. Temperature range -40°F (-40°C) to 300°F (149°C). 0-600 rpm speed range. Exclusive, non-galling Waukesha "88" alloy rotors. 3A and BISCC approved pump. Easy disassembly for easy cleaning. Flexible three-way mounting. Inlets/outlets: (2) 1 ½ in. dia. S-line Fittings. Overall dimensions: 3 ft. 2 in. L x 1 ft. W x 1 ft. 4 in. H.



