

Tri Clover 1-1/2 in. Stainless steel Throttling valve

Mfg: Tri Clover

Model: 771S-10M-14P-1.5-316L

Stock No.: HDSC264.3a

Serial No.:

Tri-Clover Pneumatic Regulating Valve. Model: 771S-10M-14P-1.5-316L. Valve is: Normally open, short stroke, lower T Tri-clamp, 316 stainless steel. The air-operated throttling valve is ideal for high volume, sanitary liquid processing applications where precision control of flow rate or pressure is required. The valves have a sanitary and flexible design allowing it to be used in a wide range of metering, blending, weighing and filling system applications. The valve is remote-controlled by means of compressed air. It has few and simple moveable parts which results in a very reliable valve. The valve is operated by means of a pneumatic actuator. Inlets/outlets: (2) 1-1/2 in. dia. S-line fittings. Overall dimensions: 1 ft. 9 in. L x 6 in. W x 5 in. H.

