

Tri-Clover C-218 Centrifugal Pump with Cart - 5 HP

Mfg: Tri-Clover

Model: C218MD18T-S

Stock No.: HDUL966A.7

Serial No.: R7155

Tri Clover Sanitary Centrifugal Pump. Model C218MD18T-S. Serial: R7155. Ladish Co. Impeller diameter: 8 inches. Max pressure: 80 PSI. Seal type: mechanical. Includes stainless steel cart. Baldor motor: 5 HP, 230/460V, 13.4/6.7 amps, 1750 RPM, 60 Hz, 3-phase, 184TC frame. Ports: 2 in. inlet / 1.5 in. outlet (tri-clamp fittings). Overall dimensions: 2 ft. 3 in. L x 1 ft. 2 in. W x 3 ft. 2 in. High.







ELECTRIC MOTORS FOR HAZARDOUS LOCATIONS

NO. **S AG 19368T**

CLASS I GROUP D - CLASS II GROUP F & G

SPEC **36E338X864G1**

CAT. NO. **CM7044T**

H.P. **5** F

VOLTS **230/460**

AMPS **13.4/6.7**

R.P.M. **1750**

CYCLE **60** PH **3** CLASS **B**

SER. F. **1.00** DES **B** COOL **A**

RATING **40C AMB-CONV**

FRANK **184TC** SER **498**

OPERATING TEMPERATURE CODE T3C

HALDOR ELECTRIC CO.
FORT SMITH, ARK. U.S.A. 19617