

## Tri Clover PR25 Positive Displacement Pump

Mfg: Tri-Clover

Model: PRR25-11/2M-TH4-ST-S

Stock No.: HDUL966B.7

Serial No.: K3767D

Used Tri Clover Rotary Lobe Positive Displacement Pump. Model: PRR25-11/2M-TH4-ST-S. Serial: K3767D. Ladish Co. A3. PR Series. Maximum flowrate at 20 PSI: 28 GPM. Pump displacement per revolution: .08 gallons. Features: pressure relief faceplate, 4-lobe stainless rotors, mechanical variable drive, wheeled base. Dodge APG drive: size DG2A, gear ratio: 11.4, final speed range: 36-283 RPM. Reliance motor: 2 HP, 1725 RPM, 208-230/460V, 5.4-5.4/2.7 amps, 3-phase, 60 Hz. Ports: 1.5 in. Tri-Clamp. Overall dimensions: 3 ft. 3 in. L x 1 ft. 5 in. W x 2 ft. High.





