

Cherry Burrell Superhomo Homogenizer

Mfg: Cherry Burrell

Model: SS-2100-VBR

Stock No. HDWD143.30

Serial No. 731297-701

Cherry Burrell Superhomo Homogenizer. Model: SS-2100-VBR. Sanitary A-3 rated. Single stage manual valve assembly. 1-1/4 in. plungers. 3000 psi. Tapered seat poppet valve cylinders. Maximum capacity: 1000 gph. S/N: 731297-701. Inlets/outlets: (2) 1-1/2 in. (2) 1-3/4 in. Reliance Motor: frame 286T, 30 hp, 1,765 rpm, 230/460 V, type P, ID No. P28G12C-G12KY, 74-37 amps, 60 Hz, 3 phase. Overall dimensions 50 in. L x 33 in. W x 51 in. H.



