

## APV Crepaco Positive Displacement Pump

Mfg: APV Crepaco

Model: R4BS

Stock No. HDWR148.17a

Serial No. 03AP454808-010

APV Crepaco Positive Displacement Pump. Model: R4BS. S/N: 03AP454808-010. Estimated flowrate at 577 RPM: 100 gpm. Nominal capacity: 160 gpm. Displacement per Revolution: 0.175 gal. Maximum Speed: 900 rpm. Seal option: O-ring seals. U.S. Electrical Motor, 7-1/2 hp, 1745 rpm, 208-230/460 V, 22.40-22.60/10.30 amps, 60 Hz, 3 phase. Drive Ratio: 3.02. RPM out: 577 (final). Inlets/outlets: (2) 2 in. dia. ACME fittings. Overall dimensions: 4 ft. 8-1/2 in. L x 1 ft. 6 in. W x 2 ft. 2 in. H.



