

DCI Pressure Wall Jacketed Processor Tank- 500 Gallon

Mfg: DCI

Model:

Stock No. HEC009.

Serial No. 89PH39122

DCI Pressure Wall Jacketed Processor Tank- 500 Gallon. S/N: 89PH39122, Nat'l Bd: 1358. Jacket MAWP @ -20°F: 40 psi. Jacket volume: 7 gal. Product contact surface: 316 stainless steel. Hinged lid, shallow cone bottom, with center agitator. Vertical agitator has (8) 12 in. L x 4 in. W paddles and (4) full-length, fixed baffles. Reuland Motor, 2.5 hp, 1800/83 rpm, 230/460 V, 7.6/3.9 amps, 60 Hz, 3 phase. Inlets: (2) 1/2 in. dia. thermowells, (4) 1-1/2 in. threaded jacket heat exchange zones, (2) 3 in. dia. Q-line clamp ports. Outlets: (2) 1 in. dia. for jacket, (1) 2 in. Q-line clamp outlet for tank. Overall dimensions: 60 in. L x 58 in. W x 9 ft. 2 in. H.

