

DCI Pressure Wall Jacketed Processor- 500 Gallon

Mfg: DCI

Model:

Stock No. HEC011.

Serial No. 86PH33112B

DCI Pressure Wall Jacketed Processor- 500 Gallon. S/N: 86PH33112B. Nat'l Bd: 814.
Jacket MAWP @ 250 °F: 70 psi. Jacket volume: 7.25 gal. 316 stainless steel product contact surface.
Hinged lid, shallow cone bottom with center agitator. Vertical agitator has (8) 12 in. L x 4 in. W paddles and (4) full length, fixed baffles. Sew Eurodrive Motor Drive, 19.22 ratio, 1700 rpm (input), 89 rpm (output), 2120 lb-in torque. Inlets: (2) 1/2 in. dia. thermowells, (1) 1-1/2 in. Q-line clamp ports for jacket, (3) 3 in. Q-Line clamp ports. Outlets: (1) 2 in. dia. for jacket, (1) 3 in. dia. for tank. Overall dimensions: 65 in. L x 57 in. W x 90 in. H.

