

SWECO Stainless Steel Separator – 48 in.

Mfg: SWECO

Model: A-1D

Stock No: HNDC248

Serial No: 892

SWECO Stainless Steel Separator. Model: A-1D. S/N: 892. (2) 48 in. diameter product / screen contact surfaces. Motor: 1 hp, 1200 rpm, 440V, 3 phase. Sweco separators offer maximum throughput and screening efficiency to many types of products by accomplished vibration over a screen cloth with varieties of mesh sizes to fit specific applications. Products and actions addressed include: sizing for dry products to include: sugars, spices, feeds, and abrasives; “scalping” to remove unwanted, oversized particles to include metal bits, blood and bone material; gravity filtering and product recovery from slurries such as ceramics; and waste water cleanup which could include brewery waste, laundry waste, or many other effluent applications. This unit was in prior service with Crane Plumbing in their porcelain processing line. (2) 8 in. discharge spouts. Top level discharge opening 13 in. L x 3 in. H. Bottom level discharge opening 11 in. L x 3.5 in. H. Overall dimensions: 4 ft. L x 4 ft. 10 in. W x 5 ft. 3-1/2 in. H.





