

Mycom/Cimco 6-Cylinder Reciprocating Compressors

Mfg: Mycom/Cimco

Model: C6-W06F

Stock No. HSCI007.

Serial No. 95771, 95772, 95773

(3) Mycom/Cimco 6-Cylinder Reciprocating Compressors. Model: C6-W06F. S/N's: 95771, 95772, and 95773. Minimum hydrostatic test pressure hi/lo: 450/300 psig. Minimum air test pressure hi/lo: 300/180 psig. Each compressor is equipped with an 18 in. dia. pulley. (3) Lincoln Compressor Motors, 125 hp, 1710 rpm, 230/460 V, 288/144 amps, 60 Hz, 3 phase. Inlets: (1) 4 in. dia. suction pipe. Outlets: (1) 3 in. dia. discharge pipe. Overall dimensions: 60 in. L x 44 in. W x 70 in. H.

