

Stainless Steel Single Shell Mix and Blend Tank with Double-Motion Side-Sweep Agitation- 5000 Gallon

Mfg:

Model:

Stock No.: IMS9703.70

Serial No.:

Stainless Steel Single Shell Mix and Blend Tank with Double-Motion Side-Sweep Agitation- 5000 Gallon. Inner agitator dimensions: 3 ft. 6 in. W x 6 ft. H. Outer agitator dimensions: 1 ft. 6 in. W x 6 ft. H. Blade dimensions: (13) 1-1/2 in. W, (3) 4 in. W. Blade spacing: 3-1/2 in. Oval manway dimensions: 2 ft. 4 in. L x 2 ft. W. Baldor Industrial Motor, 5 hp, 1725 rpm, 208-230/460 V, 15-3.21/6.6 amps, 60 Hz, 3 phase. Electra Motor Drive, 30 ratio, 6.82 hp (input), 57.5 rpm (final). Borg Warner Motor Drive, 10 ratio, 5.75 rpm (final). Borg Warner Motor Drive, 10 ratio, 5.75 rpm (final). Inlets/outlets: (1) 6 in. dia. sight glass, (1) 1/2 in. dia. recording/indicating thermometer well, (3) 3 in. dia. S-line inlets, (1) 1-1/2 in. dia. S-line outlet, (1) 4 in. dia. tank outlet. Overall dimensions: 12 ft. L x 11 ft. 7 in. W x 11 ft. H.







