

Stainless Steel Processor 3,000 Gallon

Mfg:

Model:

Stock No. cJG01.175

Serial No.

Stainless Steel Processor- 3,000 Gallon. 3 in. outlet, reduced to 2 in. valve, center bottom outlet. Inlets middle top 2 in. side top 2 in. top manway 20 in. Agitator motor 5 hp, 230/460 V, Eurogear Gear 24,200 torque 13 rpm out 1680 rpm in ratio 125.01, type KAF96DT100L4 SO880019940 0 .01.88.001. Steam connections 1.5 in. inlet and 2 in. outlet. Wide sweep no scrape. Tank dimensions: 8 ft. 6 in. dia x 12 ft. 6 in. H. 14 in. higher with agitator.

