

### Tri Clover PRS125 Positive Displacement Pump

**Mfg: Tri Clover**

**Model: PRS125-R3-TC1-ST-S**

**Stock No: JMB522C**

**Serial No: 186188-01**

Tri Clover PRS125 Positive Displacement Pump. Model: PRS125-R3-TC1-ST-S. S/N: 186188-01. Pump displacement per 100 rpm: 30 gal. Maximum capacity: 120 gpm @ maximum RPM. Seal option: Single mechanical seals. Motor, 5 hp, 1745 rpm, 230/460 V, 12.6/6.3 amps, 60 Hz, 3 phase. Speed Reducer, ratio: 8.0, 218 rpm final (pump flow at 218 RPM is 65 GPM). Inlets: (1) 9 in. L x 2-1/2 in. W rectangular infeed. Outlets: (1) 3 in. dia. sanitary bevel seat fitting. Overall dimensions: 40 in. L x 19 in. W x 24 in. H.





