



Table 12 Engineering Data

ATC Model No.*	R-717 Tons*	Fans		Weights			Refrigerant Operating Charge lbs.**	Coil Volume ft ³	Spray Pump		Remote Pump			Dimensions				
		HP	CFM	Shipping	Operating	Heaviest Section†			HP	GPM	Gallons Req'd**	Conn. Size	Operating Weight	Height H	Upper U	Lower E	Coil A	Length L
979B	695	(2)15	138,900	41,510	55,830	18,220	1,185	162	(2)5	1,600	980	(2)12"	48,010	16' 6-1/4"	10' 4-1/8"	6' 2-1/8"	47-3/4"	11' 11-3/4"
1006B	714	(2)20	157,800	36,950	50,900	15,940	995	135	(2)5	1,600	980	(2)12"	43,080	15' 9-3/4"	9' 7-5/8"	6' 2-1/8"	39-1/4"	11' 11-3/4"
1046B	743	(2)25	168,000	37,050	51,000	15,990	995	135	(2)5	1,600	980	(2)12"	43,180	15' 9-3/4"	9' 7-5/8"	6' 2-1/8"	39-1/4"	11' 11-3/4"
1077B	765	(2)30	177,000	37,250	51,200	16,090	995	135	(2)5	1,600	980	(2)12"	43,380	15' 9-3/4"	9' 7-5/8"	6' 2-1/8"	39-1/4"	11' 11-3/4"
1163B	826	(2)25	187,900	42,300	58,720	18,190	1,155	158	(2)5	1,800	1,140	(2)12"	49,660	16' 9-3/4"	9' 7-5/8"	7' 2-1/8"	39-1/4"	13' 11-3/4"
1203B	854	(2)25	182,100	48,220	65,070	21,150	1,380	188	(2)5	1,800	1,140	(2)12"	56,010	17' 6-1/4"	10' 4-1/8"	7' 2-1/8"	47-3/4"	13' 11-3/4"
1283B	911	(2)20	220,100	47,100	67,570	19,600	1,195	163	(2)7-1/2	2,400	1,440	(2)12"	55,750	17' 1-1/4"	8' 11-1/8"	8' 2-1/8"	30-3/4"	18' 0"
1364B	969	(2)25	236,700	47,200	67,670	19,650	1,195	163	(2)7-1/2	2,400	1,440	(2)12"	55,850	17' 1-1/4"	8' 11-1/8"	8' 2-1/8"	30-3/4"	18' 0"
1425B	1,012	(2)30	252,000	47,420	67,890	19,760	1,195	163	(2)7-1/2	2,400	1,440	(2)12"	56,070	17' 1-1/4"	8' 11-1/8"	8' 2-1/8"	30-3/4"	18' 0"
1495B	1,061	(2)25	229,800	53,700	74,730	22,900	1,480	202	(2)7-1/2	2,400	1,440	(2)12"	62,910	17' 9-3/4"	9' 7-5/8"	8' 2-1/8"	39-1/4"	18' 0"