

APV Crepaco Stainless Steel Holding Tank and Pump – 300 Gallons



Mfg: APV Crepaco







Model: M.H.


Stock No. KAAM0219.7a

Serial No. C-0611

APV Crepaco Stainless Steel Holding Tank and Pump . 300 Gallons. Model: M.H. S/N: C-0611. Infeed hopper diameter: 6 ft. APV Crepaco Positive Displacement Pump with Baldor Industrial Motor, 15 hp, 1760 rpm, 208-230/460 V, 40-37/18.5 amps, 60 Hz, 3 phase. Motor drive. Inlets: (1) 9 in. L x 6-1/2 in. W infeed. Outlets: (1) 4 in. dia. discharge ACME fitting. Overall dimensions: 7 ft. 11 ft. L x 6 ft. 1 in. W x 7 ft. 9 in. H.







Note: the following picture show the exact unit prior to removal.

