

Grundfos Pump

Mfg: Grundfos

Model: C-40006066E-P2-9952-15

Stock No. KBCK2001B.

Serial No. _____

Grundfos Pump. Type: CR2-60-U-G-AUUE. Model: C-40006066E-P2-9952-15. Pump capacity: 11 gpm at 220 ft., MAWP: 300 psi at 250 °F. Maximum capacities: 630 gpm at 995 ft. Working temperature: -22 to 356 °F. Baldor Industrial Motor, 1-1/2 hp, 3450 rpm, 208-230/460 V, 5-4.6/2.3 amps, 60 Hz, 3 phase. Inlet/outlet: 1-1/2 in. diameter, flange: 4-1/2 in. diameter, (4) thru-holes, center-to-center: 3-1/2 in. L. Overall dimensions: 32 in. L x 8 in. W x 62 in. H.

