

1993 Trailmobile Refrigerated Trailer R-22

Mfg: Trailmobile

Model: 01AN-1UAL

Stock No. KPSB566.38a

Serial No. 1PT01ANH3R9004750

1993 Trailmobile Refrigerated Trailer. Model: 01AN-1UAL. VIN and S/N: 1PT01ANH3R9004750. Inside dimensions: 46 ft. 9 in. L x 96 in. W x 98 in. H. GVWR: 65,000 lbs. GAWR (2 axles): 20,000 lbs. each with 11R24.5G tires, 8.25x24.5 rims, and inflated @ 95 psi. Coupler height: 49.5 in. Floor code: L. Door code: F. Side lining code: F. Trailmobile thermal performance - Heat transmission rate: 103 Btu/hr-°F. Floor airflow area: 46.3 sq. in. Carrier Transicold Phoenix Advantage Refrigeration Unit, Model: NDA749N0-WM-0, S/N: DAA90188514, Refrigerant: R-22. CFM:41 Carlyle 6-Cylinder Reciprocating Compressor, Model: 05GG041150, S/N: 2093J02322. 41 CFM Cooling (100 °F ambient): 54,000 Btuh @ 35 °F, 35,000 Btuh @ 0 °F, 20,000 Btuh @ -20 °F. Heating (0 °F ambient): 46,000 Btuh @ 65 °F, 46,000 Btuh @ 35 °F. Air discharge (no load/system load): 3,350/2,940 scfm. Aluminum floor. Outlets: (1) 48 in. W x 4 in. H air discharge, (1) 45 in. W x 89 in. H, (1) 99 in. W x 103 in. H rear door access. Diesel motor is not included, but can be added. Overall dimensions: 50 ft. L x 102 in. W x 13 ft. 2 in. L.

















