

**1990 Mycom / Reco N8B Ammonia 8-Cylinder Reciprocating Compressor – 60 HP**

**Mfg: Mycom / Reco**

**Model: N8B**

**Stock No: KWBF005**

**Serial No: MB8647**

1990 Mycom / Reco Ammonia 8-Cylinder Reciprocating Compressor. Model: N8B. S/N: MB8647. Refrigerant: R-717 (Ammonia). Displacement: 450 cfm. Bore: 5-1/8 in. Stroke: 3-15/16 in. Toshiba high efficiency electric motor - 60 HP. 1760 rpm, 230/460 V, 157/78.5 amps, 60 Hz, 3 phase. Oil pressure cut off switch. Drive pulley diameter: 12 in. Driven pulley diameter: 18 in. Pulley ratio: .67. Inlet: 4 in. suction port. Outlet: 3 in. discharge port. Overall dimensions: 7 ft. L x 4 ft. 6 in. W x 5 ft. 5 in. H. (ACN281-BC/M)



