

Mycom N8B 8-Cylinder Reciprocating Compressor – 200 HP

Mfg: Mycom

Model: N8B

Stock No: KWBF006

Serial No: MB8509

Mycom N8B 8-Cylinder Reciprocating Compressor. Model: N8B. S/N: MB8509. Refrigerant: R-717 (Ammonia). Nominal capacity: 143.8 tons at 160 bhp with a 20°F suction temperature and a 95°F condensing temperature. Displacement: 450 cfm. Max speed: 1,200 rpm. Bore: 5-1/8 in. Stroke: 3-15/16 in. Lincoln electric motor, 200 hp, 1780 rpm, 219 amps, 460 V, 60 Hz. 3 phase. Controls: (1) Penn oil pressure cut-off switch, (1) Penn suction/discharge pressure switch, (1) Penn Load/unloading automatic cut-off switch. Power supply: 460 V. Drive pulley diameter: 12 in. Driven pulley diameter: 18 in. Pulley ratio: .67. Inlet: 4 in. suction port. Outlet: 3 in. discharge port. Approximate weight: 6,530 lbs. Overall dimensions: 7 ft. x 4 ft. 8 in. W x 7 ft. 1 in. H. (ACN346-BC/Motor)





