

Reco Recirculator Package – 3 ft. 6 in. Dia. X 12 ft. 2 in. L

Mfg: Reco

Model:

Stock No.: KWBF195.2

Serial No.: W-943-1-1

Reco Recirculator Package. Nat'l Bd No. 3804. S/N: W-943-1-1. Approximate capacity: 926 gallons. Recirculator vessel inside straight-wall dimensions: 3 ft. 6 in. dia. x 12 ft. 2 in. L. MAWP: 150 psi @ 300°F. Shell thickness: 0.375 in. Head thickness: 0.375 in. Reco surge tank. Nat'l Bd: 3477. S/N: S-1737-1-12. MAWP: 300 psi @ 300°F. Shell thickness: 0.250 in. Head thickness: 0.250 in. Buffalo centrifugal pump. Model: 118-31-0073-0. S/N: DA72726EB. Sales order No. 97430427-001. Capacity: 116 gpm. MAWP: 400 psi. Motor, 10 hp, 1750 rpm, 230/460 V, 25/36.5 amps, 60 Hz, 3 phase. Viking positive displacement pump. Model: 0125. S/N: 2229315. Toshiba electric motor, 5 hp, 875 rpm, 230/460 V, 16.6/8.30 amps, 60 Hz, 3 phase. Inlets: (1) 6 in. dia. port, (1) 3 in. dia. port. Outlets: (1) 4 in. dia. port, (1) 2-1/2 in. dia. port, (2) 1 in. dia. ports. Overall dimensions: 13 ft. L x 5 ft. 6 in. W x 9 ft. 1 in. H.













