

Westinghouse Easy Start 100 Starter Control Panel – 200 HP

Mfg: Westinghouse

Model: EJ 270-4NR

Stock No: KWBF502A

Serial No: 2357

Westinghouse Easy Start 100 Starter Control Panel. Model: EJ270-4NR. S/N: 2357. Power supply: 208-230/460 V, 270 amps, 50/60 Hz. 3 phase. HP rating: 75 hp at 208V, 100 hp at 230V and 200 hp at 460V. Hours: 1537.5. Enclosure: NEMA 1. Overall dimensions: 2 ft. 6 in. L x 1 ft. 4 in. W x 3 ft. 8-1/2 in. H.





FORM 1200-246
65340272246

IMPORTANT WARRANTY REGISTRATION CARD

This card will serve as a record of your warranty registration and will enable expedited handling of any warranty claims. Please fill in and return.

MODEL 53270-4NR
SERIAL 2357 D.C. 745011
COMPANY _____
Address _____
City _____

PURCHASED FROM: _____

Date of Purchase/Installation _____



INSTALLATION: New Retrofit
 Existing

MOTOR: New Existing

APPLICATION: Conveyor Compressor
 Fan Pump
 Machine Tool Motor
 OTHER _____

Solid State Starters in Plant: 0 1-5 6-19 Over 20

Variable Frequency Drivers in Plant: 0 1-5 6-19 Over 20



MODEL NUMBERS CONT.

OPEN PANEL	ENCLOSED	AMPS	VOLTS	HP*			
				208V	230V	460V	575V
EJ190-3NC	N/A	190	380/415				
EJ190-4NC	N/A	190	208/230/460	60	75	150	
EJ190-5NC	N/A	190	500/575				150
EJ270-3NP	EJ270-3NR	270	380/415				
EJ270-4NP	EJ270-4NR	270	208/230/460	75	100	200	
EJ270-5NP	EJ270-5NR	270	500/575				250
EJ270-3NC	N/A	270	380/415				
EJ270-4NC	N/A	270	208/230/460	75	100	200	
EJ270-5NC	N/A	270	500/575				250
EJ390-3NP	EJ390-3NR	390	380/415				
EJ390-4NP	EJ390-4NR	390	208/230/460	125	150	300	
EJ390-5NP	EJ390-5NR	390	500/575				350
EJ390-3NC	N/A	390	380/415				
EJ390-4NC	N/A	390	380/415				

Figure 2-4. Starts-Per-Hour EJ270

Model Number EJ270			Starts-Per-Hour				
Curr. Limit	Starting Current AC Amps	Start Time Sec.	Percent Off-Time				
			0%	10%	20%	30%	
250%	675	2	120	180	240	300	
		5	40	60	100	135	
		10	20	30	50	60	
300%	910	2	40	80	120	160	
		5	20	40	60	80	
		10	12	20	30	40	
400%	1080	2	20	40	80	120	
		5	8	16	24	40	
		10	4	8	12	20	
500%	1350	2	10	20	40	60	
		5	2	4	8	16	
		10	-	2	6	12	

2-5