

Toshiba High Efficiency Electrical Motor - 200 HP

Mfg: Toshiba

Model: B2004VLF4UD

Stock No.: KWBF503B

Serial No.: 9408197A

Toshiba High Efficiency Electrical Motor – 200 HP. Model: B2004VLF4UD. S/N: 9408197A. Motor specifications: 1770 rpm, 230/460 V, 232/464 amps, 60 Hz, 3 phase. Frame: 445T. Insulation class: F. Nema design: B. Code: G. Type: TIKK. Shaft diameter: 3 .375 in. Overall dimensions: 3 ft. 6 in. L x 2 ft. 1 in. W. x 2 ft. 3 in. H.



