

Toshiba High Efficiency Electrical Motor – 200 HP

Mfg: Toshiba

Model: B2004VLF4UD

Stock No: KWBF503D

Serial No: 9408196A

Toshiba High Efficiency Electrical Motor – 200 HP. Model: B2004VLF4UD. S/N: 9408196A. Motor specifications: 1770 rpm, 230/460 V, 232/464 amps, 60 Hz, 3 phase. Frame: 445T. Insulation class: F. Nema design: B. Code: G. Type: TIKK. Shaft diameter: 3.250 in. Overall dimensions: 3 ft. 4 in. L x 1 ft. 11 in. W. x 2 ft. 2 in. H.



