

Ideal Electric Motor-5 HP

Mfg: Ideal Electric

Model:

Stock No.: KWBF750M

Serial No.: 179859

Ideal Electric Motor- 5 HP. S/N: 179859. Motor specifications: 1740 rpm, 220/440 V, 13.2/16.6 amps, 60 Hz, 3 phase. Frame: 254. Code: G. Shaft diameter: 1 in. Overall dimensions: 1 ft. 7 in. L x 1 ft. 3 in. W x 1 ft. 1 in. H.





GENERAL ELECTRIC
MOTOR

179855	NO. 251	DESIGN AT TORRE C
NO. 220-440	PH. 3	SERVO FACTOR 15 IN 10% TORQUE MOTOR
1740	13.2-6.6	IMP. 40% CCMT
		TEMP. 105

SHOULD BE LUBRICATED BY LUBRICATING OIL EVERY YEAR OR
EQUIVALENT. OIL SHOULD BE EXTERIOR BEARING SHEET
OR STAINLESS STEEL. PLEASE WITH CLEAN OIL. OIL SHOULD
BE FILLED TO TWO THIRD FULL OF NORMAL OIL. OIL
SHOULD BE CONDUIT BOX COVER OR WINDING BOX