

1994 Jordan Vessel Company Ammonia Thermosyphon Receiver – 275 Gallon

Mfg: Jordan Vessel Company

Model: HTR 24-12

Stock No: LCNM010

Serial No: 94-874

1994 Jordan Vessel Company Ammonia Thermosyphon Receiver. Model: HTR 24-12. S/N: 94-874. Nat'l Bd: 841. Approximate capacity: 275 gallons. Inside straight-wall dimensions: 24 in. dia. x 12 ft. L. MAWP: 250 psi @ 650°F. MDMT: -20°F @ 250 psi. Inlets: (1) 5 in. dia. port, (1) 4 in. dia. port, (2) 2-1/2 in. dia. ports. Outlets: (1) 1 in. dia. relief port, (1) 3/4 in. dia. gauge port, (1) 4 in. dia. port, (1) 2 in. dia. port, (1) 1 in. dia. port, (1) 1/2 in. dia. port. Overall dimensions: 12 ft. 2 in. L x 3 ft. 3 in. W x 2 ft. 11 in. H.

