

Carrier Chiller Model 30GB075650

Mfg: Carrier

Model: 30GB075650

Stock No. LEPH04.

Serial No. T698198

Carrier Chiller. Model 30GB075650. S/N T698198. Min circuit amps: 187.3.
 Max overcurrent protective device 225 fuse only. Control power supply: 115 V, 1 phase, 60 Hz 20 amps.
 (factory

	Qty	Volts	Phase	Hz	RLA	LRA	Refrig-R22	charged)
Compressor 1:	2	460	3	60	60	52.1	253	122 lbs
Compressor 2 :	1	460	3	60	52.1	253	70 lbs	

	Design/Test Pressure	
High:	450 psi	3103 kpa
Low:	235 psi	1620 kpa

Fan Motors:	Qty	Volts	Phase	Hz	FLA	HP	KW out
	6	460	3	60	3	1.75 NEC	1.31

Heaters:	Volts	Phase	Hz	permissible voltage at unit:	
	460	3	60	508 max	414 min

