

## 2000 McQuay Air Cooled Chiller-350 Tons

Mfg: McQuay

Model: ALS370BS-27ER10

Stock No. LSHD001.

Serial No. STNU000600277

2000 McQuay Air Cooled Chiller-350 Tons. Model: ALS370BS-27ER10. S/N: STNU000600277. Refrigerant R-22, max pressure 300 psi. Power supply 460V, 60Hz, 3phase. (24) Condenser fans, 2.0 HP motor, 28 in. dia. 1140 rpm, 60 Hz. High efficiency fin and tube type condensers with integral sub cooler, (12) fins per in. and 4 rows deep. Baffled Shell and Through Tube, Direct Expansion Evaporator, Water Vol. 107 gallons, Max. water pressure 175 psi. Each unit consists of multiple air cooled condensers with integral sub cooler sections, multiple accessible semi-hermetic single-screw compressors, replaceable tube multiple circuit shell-and-tube evaporator, and complete refrigerant piping. Other features include compressor heaters, an evaporator heater for low ambient water freeze protection, automatic, one time pump down of refrigerant circuit upon circuit shutdown, and an advanced fully integrated microprocessor control system. Overall Dimensions: 459 in. L x 83.4 in. W x 94.5 in. H. Weight 22,050 lbs.





